



Variateurs à coupure de phase Dynalite

DLE410

4 channel Leading Edge Dimmer Controller with a maximum load per channel of 10 A.


The Philips Dynalite DLE410 is a four channel leading edge dimmer controller, with a maximum load per channel of 10 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge electronic transformers. - Ideal for applications where multiple user settings are required
Interference suppression
Naturally ventilated
Soft start and voltage regulation technologies
Diagnostic functionality
User controls
Options available

Données du produit


Caractéristiques générales		Nom du produit de la commande	DLE410
Marquage CE	Marquage CE	Code barre produit	8710163505268
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options	Code de commande	50526800
Conforme à la directive RoHS UE	Oui	Code de commande local	DLE410
Conditions d'utilisation		Numérateur - Quantité par kit	1
Plage de températures ambiantes	0 à +40 °C	Conditionnement par carton	1
Données logistiques		SAP - Matériaux	913703006009
Code de produit complet	871016350526800	Poids net (pièce)	8,450 kg

Variateurs à coupure de phase Dynalite

Schéma dimensionnel



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

