

Technical Data and Lamp Matrix												
Lamp Wattage	Lamp Type	Product description	12NC	Input power (W)	Lamp power (W)	Ploss (W)	THD (%)	Power Factor	EEl	Tc Point Max.	Ambient Temperature Ta	BLF
2x36W	T8	HF-Regulator 236 TL-D EII	913700609366	73	32	9,00	6,30	0,98	A1 BAT	75°C	-20 °C to +50 °C	1,0
2x36W	PL-L			69	30	9,00	6,60	0,98	A1 BAT	75°C	-20 °C to +50 °C	0,97

