



# Accessoires Luminaires Gestion Locale

## LCA8005/00 ActiLume Mounting Clip 50 W

White clip to be used for ActiLume multisensor, ActiLume Luminaire based extension sensor, ActiLume 1-10V sensor and the ActiLume MicroLuxSense. With this clip the sensor can be mounted in the luminaire housing.

White clip to be used for ActiLume multisensor, ActiLume Luminaire based extension sensor, ActiLume 1-10V sensor and the ActiLume MicroLuxSense. With this clip the sensor can be mounted in the luminaire housing.

### Données du produit

Données logistiques		Numérateur SAP - Quantité par kit	
Code de produit complet	871829171963200		1
Nom du produit de la commande	LCA8005/05 ActiLume Mounting Clip 50 W	SAP - Conditionnement par carton	41
Code barre produit	8718291719649	Code 12NC	913700355103
Code de commande	71963200	Poids net (pièce)	4,600 g
Code de commande local	LCA8005/05W		

## Accessoires Luminaire Gestion Locale

### Schéma dimensionnel



#### Product

LCA8005/05 ActiLume Mounting Clip 50 W

LCA8005/05 ActiLume Mounting Clip 50 W

