



Variateurs à coupure de phase Dynalite

DLE1210GL

12 channel Leading Edge dimmer with a maximum load per channel of 10 A.


The Philips Dynalite DLE1210GL is a 12 channel leading edge dimmer controller, with a maximum load per channel of 10 A and total device load of 75 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge dimmable electronic transformers. - Large load capability DMX512 compatibility Interference suppression Naturally ventilated Soft start and voltage regulation technologies Diagnostic functionality User controls Option available

Données du produit

Caractéristiques générales		Nom du produit de la commande	DLE1210GL
Marquage CE	Marquage CE	Code barre produit	8710163505688
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options	Code de commande	50568800
Conforme à la directive RoHS UE	Oui	Code de commande local	DLE1210GL
Conditions d'utilisation		Numérateur SAP - Quantité par kit	1
Plage de températures ambiantes	0 à +40 °C	SAP - Conditionnement par carton	1
Données logistiques		Code 12NC	913703014009
Code de produit complet	871016350568800	Poids net (pièce)	16,000 kg

Variateurs à coupure de phase Dynalite

Schéma dimensionnel



Dynalite Leading Edge Dimmers

