



# Variateurs à coupure de phase Dynalite

## DDLE801

8 channel Leading Edge Dimmer Controller at 1 A per channel


The Philips Dynalite DDLE801 supports eight channels of leading edge dimming at 1 A per channel. - It is suitable for use with incandescent lighting, as well as leading edge compatible magnetic and electronic transformers. - Advanced LED dimming technology makes the unit particularly suited to residential, retail and hospitality applications. - Active Load technology on each channelSoft start and voltage regulation technologiesSuperior internal drive componentry tuningFlexible mounting solution

### Données du produit

Caractéristiques générales	
Marquage CE	Marquage CE
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options
Conforme à la directive RoHS UE	Oui
Conditions d'utilisation	
Plage de températures ambiantes	-5 à +40 °C
Données logistiques	
Code de produit complet	871869600136300
Nom du produit de la commande	DDLE801
Code barre produit	8718696001363
Code de commande	00136300
Code de commande local	DDLE801
Numérateur - Quantité par kit	1
SAP - Conditionnement par carton	1
Code 12NC	913703061509
SAP - Poids net (pièce)	633,000 g

## Variateurs à coupure de phase Dynalite

### Schéma dimensionnel



Dynalite Leading Edge Dimmers

